

SUSCOM

AP CHAIR RANGE



SUSCOM | ABOUT US

At Suscom we focus and strive to meet our client's demands, for this reason, our in-house facilities allow us to be flexible and give us greater control over quality.

We believe that design and innovation is the key to our success. Our new production facilities is the first of its kind, with the option of automated castor fitting allowing us to tailor each product to suit our clients requirements.

As a company focused on lowering our environmental impact, it is important that our products also incorporate and reflect this ethos. With all of this in mind we have modified and updated many products to make them 100% recyclable.



AP | ABOUT


Designed for the changing needs of today's modern workplaces, the AP Chair is a multi-purpose office chair specially designed for shared workstations, hot desking, conference rooms and collaborative spaces.



AP | TILT



AP TILT | EXPLODED




AP TILT | OPTIONS

- | | | |
|-----|--------------------|---|
| 1. | SHELL-AP.BLK | AP Shell Black with Black L/R PU Pads |
| 2. | SHELL-AP.LG | AP Shell Light Grey with Grey L/R PU Pads |
| 3. | SHELL-AP.LINER | Fabric Seat Liner |
| 4. | MEC-COMPACT | Tilting Mechanism |
| 5. | SHELL-AP.COVER.GRY | AP Grey Mech Cover |
| 6. | KGL.41335030C6141 | Short Management Gas Spindle Black |
| 7. | KGL.31005040S443 | 7 x 50 DC Chrome Gas Class 4 |
| 8. | B-3-690 | Black Nylon Base |
| 9. | BAS-3-690.ALU | Aluminium Base |
| 10. | CAS-NT.60.23 | 60MM Castor |





AP FIXED | EXPLODED



AP FIXED | OPTIONS


- | | | |
|----|-------------------|---|
| 1. | SHELL-AP.BLK | AP Shell Black with Black L/R PU Pads |
| 2. | SHELL-AP.LG | AP Shell Light Grey with Grey L/R PU Pads |
| 3. | SHELL-AP.LINER | Fabric Seat Liner |
| 4. | MEC-AP.FIXED | Fixed Black Mechanism Plate |
| 5. | KGL.41335030C6141 | Short Management Gas Spindle Black |
| 6. | KGL.31005040S443 | 7 x 50 DC Chrome Gas Class 4 |
| 7. | B-3-690 | Black Nylon Base |
| 8. | BAS-3-690.ALU | Aluminium Base |
| 9. | CAS-NT.60.23 | 60MM Castor |



AP | 4 LEG



AP 4 LEG | EXPLODED



AP 4 LEG | OPTIONS


- | | | |
|----|-----------------|---|
| 1. | SHELL-AP.BLK | AP Shell Black with Black L/R PU Pads |
| 2. | SHELL-AP.LG | AP Shell Light Grey with Grey L/R PU Pads |
| 3. | SHELL-AP.LINER | Fabric Seat Liner |
| 4. | FME-AP.4LEG.CAP | 4 Leg Feet, X4 required per Frame |
| 5. | FME-AP.4LEG.BLK | Black AP 4 Leg Frame |
| 6. | FME-AP.4LEG.CRM | Chrome AP 4 Leg Frame |



AP | CANTILEVER



AP CANTILEVER | EXPLODED



AP CANTILEVER | OPTIONS

- | | | |
|----|------------------|---|
| 1. | SHELL-AP.BLK | AP Shell Black with Black L/R PU Pads |
| 2. | SHELL-AP.LG | AP Shell Light Grey with Grey L/R PU Pads |
| 3. | SHELL-AP.LINER | Fabric Seat Liner |
| 4. | FME-AP.CANT.CAP | Cantilever Cap, X2 Required per Frame |
| 5. | FME-AP.CANT. GLI | Cantilever Glides, X4 Required per Frame |
| 6. | FME-AP.CANT.BLK | Black AP Cantilever Frame |
| 7. | FME-AP.CANT.CRM | Chrome AP Cantilever Frame |





Suscom Industries Ltd.

Unit 8 Leopold Street | Lamberhead Ind. Estate
Pemberton | Wigan | WN5 8DH | United Kingdom

Web | www.suscom-ind.co.uk

Telephone | +44 (0)1942 221133

Email | sales@suscom-ind.co.uk

